

EAF-150

Description

Sensor Activated Electronic Hand Washing Faucet for pre-tempered or hot and cold water operation.

Battery Powered Models

□ EAF-150 Single Supply Faucet (For pre-mixed water only)

☐ EAF-150-IC Single Supply Faucet (For pre-mixed water only) and

i.q.-Click Feature

☐ EAF-150-ISM With Integral Spout Temperature Mixer

(For Hot and Cold water supply connection) With Integral Spout Temperature Mixer

□ EAF-150-ISM-IC With Integral Spout Tem and *i.a.-Click* Feature

□ EAF-150-ISM-DPU-IC With Integral Spout Temperature Mixer,
Drain Pop Up and *i.q.-Click* Feature

► Flow Rate

☐ 2.2 gpm/8.3 Lpm Max. Flow Aerator

Specifications

Sensor Activated, Electronic, Chrome Plated Die-Cast Metal, Hand Washing Faucet with the following features:

- Modular One-piece Construction with all Concealed Components above deck
- Double Infrared Sensors with Automatic Setup and Indicator Light
- Automatic Self-adapting Sensor Technology
- · Low Battery Indicator
- Magnetic Solenoid Valve
- Water Supply Connection with Flexible High-pressure Hose and Strainer
- 6 volt Lithium 2CR5 Commercial Battery included
- Appropriate Mounting Hardware included
- Optional 24 Hour Sentinel Activation

Variations

	Integral Spout Mixer
□IC	<i>i.qClick</i> feature
□ DPU	Drain Pop Up

Accessories

Trim Plates

□ ETF-607-A Trim Plate for 4" (102 mm) Centerset Sink
□ ETF-608-A Trim Plate for 8" (204 mm) Centerset Sink

Trim Plates must be specified and ordered separately.

Aerator

0.5 gpm/1.9 Lpm Max. Spray Head

Warranty

3 year (limited)

☐ EAF-12

► ADA Compliant

Compliant to:

ASME A112.18.1







EAF-150-ISM



EAF-150-ISM-IC



EAF-150-ISM-DPU-IC

The Optima *i.g.* faucet — Bringing intelligence to water

Sloan's Optima *t.q.* EAF-150 Series electronic hand washing faucets operate by means of a dual infrared sensor and microprocessor based logic that utilize self-adapting technology to ensure superior performance. The modular design incorporates all of the operating components of the faucet, including the sensor, solenoid, circuitry and battery above the sink within a die-cast metal spout.

ISM models feature an integral temperature control lever which allows the user to adjust the water temperature. This adjustment can also be converted to a fixed setting. EAF faucets ordered without the ISM variation must be connected to a single, pre-tempered water supply.

The *I.q.-Click* feature allows the user to place the faucet into optional function modes, including "continuous run" and "temporary off" simply by pressing a button on the spout. The use of the *I.q.-Click* feature is recommended only in installations where users have a regular familiarity with the faucet (i.e., executive and non-public rest rooms). Models furnished with the *I.q.-Click* feature are also available with a Pop Up Drain.

Optima £q EAF-150 series faucets include a 6 VDC lithium battery. Battery life is approximately three (3) years.



Listed by I.A.P.M.O.



This space for Architect/Engineer approval			
Job Name	Date		
Model Specified	Quantity		
Variations Specified			
Customer/Wholesaler			
Contractor			
Architect			

EAF-150

Description

Sensor Activated Electronic Hand Washing Faucet for pre-tempered or hot and cold water operation.

Flow Rate

☐ 2.2 gpm/8.3 Lpm Max. Flow Aerator

ELECTRICAL SPECIFICATIONS

Control Circuit

6 VDC — Includes Auto Set Range Adjustment and Low Battery Indicator LED

Sensor Range Nominal:

4" - 5" (102 mm - 127 mm) Faucet Adaptive Self-adjustment Range:


2" - 14" (51 mm - 356 mm) nominal


Power Supply

6 VDC Lithium 2CR5 battery. Approximate 3 year life

Time Out Setting

2 minutes — Maximum time faucet will run upon continuous detection (except for i.q.-click models that are otherwise set in continuous





OPERATION

As the user's hands enter the beam's effective range, the beam is reflected back into the sensor receiver and activates the solenoid valve allowing water to flow from the faucet. Water will flow until the hands are removed or until the faucet reaches its automatic time out limit setting.



1.q.-Click FEATURE

The *i.q.-Click* is a button that extends from the underside of the faucet spout that allows the user to place the faucet into the following function modes: Continuous Run, Temporary Off, Permanent Off and Auto Set Range Adjustment.

Because the use of the *i.q.-Click* feature requires familiarity with the faucet, this feature is <u>not</u> recommended for faucets intended for use by the general public. The *i.q.-Click* is ideal for use in hospital rooms, executive rest rooms and other locations where the primary user has regular contact with the product.

1.q.-Click SETTINGS


Function	Press Button	LED Signal
Continuous Run — 2 minute default setting (adjustable from 1 - 20 minutes)	1 time for 2 seconds	5 short flashes
reset:	1 time or will reset automatically after 2 minutes	
Temporary Off	2 times (double click)	5 short flashes followed by periodic flashing
reset:	1 time or will reset automatically after 2 minutes	
Permanent Off	Consult Factory	Periodic flashing and then 2 long flashes
reset:	1 time	
Auto Set Range Adjustment	2 times (double click) and then 1 time for 5 seconds	5 short flashes followed by 4 short flashes

ROUGH-IN

EAF-150 AND EAF-150-IC Faucets with Single Line Water Supply

SPOLIT 1-3/16" (30 mm) MIN. DIA. HOLE REQUIRED O-RING 1-1/2" (38 mm) GASKET MAX. DECK THICKNESS RETAINER 13" (330 mm) NUT LONG FLEX HOSE If a connection to separate hot and cold water supplies is desired, then TEMPERED back checks and a tee fitting (not SUPPLY supplied) must be used prior to connecting to the faucet.

EAF-150-ISM, EAF-150-ISM-IC AND EAF-150-ISM-DPU-IC Faucets with Hot and Cold Water Supply



When the EAF faucet is installed on a sink that has three (3) hole punchings, a Trim Plate should be used. *Trim Plates must be* specified and ordered separately:

ETF-607-A

Trim Plate for 4" (102 mm) Centerset Sink

ETF-608-A

Trim Plate for 8" (204 mm) Centerset Sink

SLOAN VALVE COMPANY • 10500 SEYMOUR AVENUE • FRANKLIN PARK, IL 60131

Phone: 1-800-982-5839 or 1-847-671-4300 • Fax: 1-800-447-8329 or 1-847-671-4380 • www.sloanvalve.com