

WINGITS® MODERN Elegance™

Structural 18/8 Stainless Steel Grab Bar

Model: WGB5ME

Part Numbers:

WGB5MEPS6 6" Polished Finish	WGB5MESN6 6" Satin Finish
WGB5MEPS8 8" Polished Finish	WGB5MESN8 8" Satin Finish
WGB5MEPS12 12" Polished Finish	WGB5MESN12 12" Satin Finish
WGB5MEPS16 16" Polished Finish	WGB5MESN16 16" Satin Finish
WGB5MEPS18 18" Polished Finish	WGB5MESN18 18" Satin Finish
WGB5MEPS24 24" Polished Finish	WGB5MESN24 24" Satin Finish
WGB5MEPS30 30" Polished Finish	WGB5MESN30 30" Satin Finish
WGB5MEPS32 32" Polished Finish	WGB5MESN32 32" Satin Finish
WGB5MEPS36 36" Polished Finish	WGB5MESN36 36" Satin Finish
WGB5MEPS42 42" Polished Finish	WGB5MESN42 42" Satin Finish
WGB5MEPS48 48" Polished Finish	WGB5MESN48 48" Satin Finish
WGB5MEPS54* 54" Polished Finish	WGB5MESN54* 54" Satin Finish
WGB5MEPS60* 60" Polished Finish	WGB5MESN60* 60" Satin Finish

*Grab Bars include center support.



Contemporary design combines with **PATENTED** BridgeBind™ Technology resulting in a Grab Bar with:


- Structural Stainless Steel
- Beauty-Functionality-Durability
- No lines for dirt to collect - maintenance free
- Unparalleled strength

BridgeBind™ Technology is the result of drilling a hole completely through stainless steel tubing, inserting a solid stainless steel pin, and HeliArc welding the pin to the far point of the tube; solidifying the pin and tube into one piece. Creating the ultimate structural bond.


MECHANICAL DATA
Width: See product part number for width. Complete length of Grab Bar is usable surface.
Diameter: 1.25" (3.2cm)
PRODUCT COMPOSITION
Entire product is 18/8 (304) stainless steel. Solid caps and pins are HeliArc welded to 18 gauge tube.
MODALITY
Use: Wall Installation.
Load Capability: 800 lbs (362.9kg)
INSTALLATION
WingIts® MODERN Elegance™ Structural Stainless Steel Grab Bars are designed to hold live loads and must be installed into adequate structural blocking or with WingIts® Grab Bar Fasteners (GBWME40).
CERTIFICATIONS
WingIts® MODERN Elegance™ Structural Stainless Steel Grab Bars meet or exceed the applicable requirements of all building codes, ADA criteria, and 2010 ADAAG and 2009 ANSI standards.
RECOMMENDED INTEGRATION
For hollow wall construction, it is recommended that WingIts® Grab Bar Fasteners (GBWME40) are used with this product. See Fastener instructions for applications.

20140819_rev6

WINGITS®



INCLUDED HARDWARE



OPTIONAL HARDWARE (Sold Separately)

