

# Home Care Technical Specification


Suction Shower Holder

LR2310W

## Stock Numbers:

- LR2310W – Suction Shower Holder

## Dimensions:



## Materials:

Suction Shower Holder is made from ABS plastic

## Installation Instructions:

1. Before attaching to a surface, check the suction cup to ensure it is clean from any debris.
2. Press the suction shower holder on a clean, smooth, dry surface. Ensure the surface is flat, clean, dry, and smooth and that it does not overlap any grout lines. Not to be used on painted surfaces. I.e. Drywall.
3. While pressing the shower holder to the surface, pull down the gray locking lever until it locks into place.

Stock Number: \_\_\_\_\_ Suction Shower Holder By Creative Specialties



25300 AL MOEN DRIVE • NORTH OLMSTED, OH 44070  
CORPORATE HEADQUARTERS: (800) 321-8809 • FAX: (800) 848-6636  
INTERNATIONAL: (440) 962-2000 • FAX: (440) 962-2726  
CUSTOMER SERVICE (USA): 800-882-0116 • FAX: (888) 379-2720  
©Copyright Creative Specialties International

BA1612